





Fujikura 90S Fusion Splicer

The 90S is the latest core alignment splicer from Fujikura. It's designed to give you high quality splices and to stay in the field. The 90S kit solves common problems seen in the field today, from splicing poor quality legacy fiber to automated equipment maintenance and upkeep. The 90S can be utilized in any field splicing application seen today: bend-insensitive fibers in drop cables, long-haul terrestrial and submarine LEAF fibers, loose buffer fiber, splice on connectors, and the list goes on. The speed and accuracy of the 90S even make it suitable for certain production and specialty environments, where high output, tight packaging, and low loss requirements are needed. Regardless your scenario, the 90S is designed to keep you going with an extended battery life of 300 splice and heat cycles, and by alleviating the need for traditional operation tasks such as; frequent arc calibrations, cleaver blade rotations, cleaver usage tracking, and manual splicing operations with its multiple automated and ease-of-use features. A redesigned work tray, cooling tray, and optional cable clamp make the 90S kit more versatile than any of its predecessors in adapting to varying work conditions and environments. In addition, if you are splicing loose buffer fiber, there is no longer a need to purchase and swap out with an additional sheath clamp. Now, a universal sheath clamp that handles both loose and tight buffer fiber is standard. Put our 90S to the test by contacting us to see its capabilities first-hand, 1-800-235-3423.



Wind Protector Open

Features

- Cleaver tracking and upkeep with wireless communication
- Automated wind protector, sheath clamps and splice operation
- Loose and tight buffer with same sheath clamp
- Lithium-ion battery with 300 splices/shrinks per charge
- Graphical User Interface with 5.0" Touchscreen
- PC software and 90S manual downloaded from splicer
- Multi-function transit case with integrated workstation

Applications

- Distribution fiber repair
- Long-haul network installation
- Field termination with splice-on connectors
- Access network installation
- Fanout kits, pigtails and splice cassettes
- OSP cable installation and repair
- Optical modules splitters, couplers, MUXs, EDFAs and attenuators







Fujikura 90S Fusion Splicer

Ordering Information

DESCRIPTION	AFL NO.
90S Fusion Splicer (machine only) Includes: Includes: ADC-20 AC Adapter, ACC-14 AC Cord, BTR-15 Battery, ELCT2-16B Spare Electrodes (pair), Sheath Clamps,	S017519
SP-03 Fiber Holder Set Plates, USB-01 Cable, Alcohol Dispenser, Screwdriver, Splicer Carrying Strap, Quick Reference Guide, TS-03 Tripod Screw, Work Tray J-Plate, SS03 single fiber stripper and CC39 Transit Case with Carrying Strap	
90S Fusion Splicer Kit (with cleaver) Includes: CT50 Cleaver, ADC-20 AC Adapter, ACC-14 AC Cord, BTR-15 Battery, ELCT2-16B Spare Electrodes (pair), Sheath Clamps, SP-03 Fiber Holder Set Plates, USB-01 Cable, Alcohol Dispenser, Screwdriver, Splicer Carrying Strap, Quick Reference Guide, TS-03 Tripod Screw, Work Tray J-Plate, SS03 single fiber stripper and CC39 Transit Case with Carrying Strap	S017521
90S Fusion Splicer without Bluetooth (machine only) Includes: ADC-20 AC Adapter, BTR-15 Battery, ACC-14 AC Cord, ELCT2-16B Spare Electrodes (pair), Sheath Clamps, SP-03 Fiber Holder Set Plates, USB-01 Cable, Alcohol Dispenser, Screwdriver, Splicer Carrying Strap, Quick Reference Guide, TS-03 Tripod Screw, Work Tray J-Plate, SS03 Single Fiber Stripper and CC39 Transit Case with Carrying Strap	S017520
One Year Extended Warranty	S012996
Two Year Extended Warranty	S013000

Recommended Products for the 90S

DESCRIPTION	AFL NO.			
Cleavers				
CT08 Cleaver	S017004			
CT50 Cleaver	S017030			
Fiber Holders (pair)				
FH-70-250 (250 µm coated fiber)	S017111			
FH-70-900 (900 µm jacketed fiber)	S017113			
FH-70-160 (160 µm coated fiber)	S017095			
FH-60-LT900 (Loose buffer 900 μm fiber)	S015181			
FH-60-LT900 (each)	S015275			
FUSEConnect® Accessories				
FH-FC-20 (900 µm within 2.0 mm sheathing) (each)	S014696			
FH-FC-30 (900 µm within 3.0 mm sheathing) (pair)	S014695			
FH-FC-900 (900 μm cable) (each)	S014697			
CLAMP-FC-2000 (pair)	S014705			
CLAMP-FC-3000 (pair)	S014704			
Power Supply Options and Equipment				
ADC-20 AC Adapter	S017513			
ACC-14 AC Power Cord	S014536			
BTR-15 Battery	S017512			
DCC-20 Power Cord	S017527			
(connects AC Adapter to cigarette lighter socket)				
DCC-21 Power Cord S017				
(connects AC Adapter to power source via alligator clips)				
DCA-03 DC Adapter (Connect AC Adaptor without battery)	S017526			

DESCRIPTION	AFL NO.
Miscellaneous	
SS03 Single fiber stripper (3 hole)	S017098
SS01 Single fiber stripper (1 hole)	S017099
ELCT2-16B Electrodes	S017103
SP-03 Fiber Holder Set Plates	S017518
Portable Tripod Workstation (see product profile for more detail)	S014773
ASW-02 Splicing Workstation (see product profile for more detail)	S010532
WT-09R Work Tray Right	S017515
WT-09L Work Tray Left	S017516
JP-09 Work Tray J-Plate	S017517
JP-10 J-Plate (Cooling tray attaches to splicer)	S017522
JP-10-FC J-Plate with Fiber Clamps	S017523
TS-03 Tripod Screw (90 Series)	S017524
ST-02 Fusion Splicer Strap	S017525
CLAMP-DC-12 (Drop cable clamp for work tray)	S017550
USB-01 Cable	S014777
CC39 Transit Case	S017514
Splicer V-Groove Cleaning Kit	S014397



Fiber Holders

- Wide range of sizes for various applications
- Loose & Tight Buffer options available



Portal Tripod Work Station

- Sturdy work tray supports the splicer, cleaver and accessories
- Tripod supports a load capacity of up to eleven pounds



V-Groove Cleaning Kit

- Removes environmental contamination from the v-groove of the splicer
- Maintains performance and ensures fiber alignment



Fujikura 90S Fusion Splicer

Specifications

PARAMETER		VALUE	
Fiber Alignment Method		Active core alignment	
Fiber Count Can Be Spliced		Single fiber	
Tibel Coulit Call be Spliced	Fiber Type	Single mode optical fiber	
Applicable Fiber	Tibel Type	Multi mode optical fiber	
	Cladding Dia.	80 to 150 um	
	Clauding Dia.	Coating dia.: Max. 3,000 µm	
Applicable Coating	Sheath Clamp		
3	·	Cleave length : 5 to 16 mm ITU-T G.652 : Avg. 0.02 dB	
Fiber Splice Performance			
	Colica Loca	ITU-T G.651 : Avg. 0.01 dB	
	Splice Loss	ITU-T G.653 : Avg. 0.04 dB ITU-T G.655 : Avg. 0.04 dB	
		ITU-T G.657 : Avg. 0.02 dB	
	Splice Loss	SM FAST mode : Avg. 8 to 10 sec.	
	· ·	AUTO mode : Avg. 14 to 16 sec.	
Applicable Protection Sleeve	Sleeve Type	Heat-shrinkable sleeve	
	Sleeve Length	Max. 66 mm	
	Sleeve Dia.	Max. 6.0 mm before shrinking	
Sleeve Heat Performance	Heat Time	60 mm slim mode : Avg. 9 to 10 sec.	
Fiber Tensile Test 5		60 mm mode : Avg. 13 to 15 sec.	
Fiber Tensile Test Force		Approx. 2.0 N	
Electrode Life	Discoursiana M	Approx. 5,000 splices	
	Dimensions W	Approx.170 mm without projection	
Physical Description	Dimensions D	Approx.173 mm without projection	
,	Dimensions H	Approx.150 mm without projection	
	Weight	Approx. 2.8 kg including battery	
	Temperature	Operate : -10 to 50 degree C	
- 1 - 10		Storage : -40 to 80 degree C	
Environmental Condition	Humidity	Operate: 0 to 95% RH non-condensing	
	•	Storage: 0 to 95% RH non-condensing	
	Altitude	Max. 5,000 m	
Ac Adaptor	Input	AC100 to 240 V, 50/60 Hz, Max. 1.5 A	
	Туре	Rechargeable Lithium Ion	
	Output	Approx. DC14.4V / 6,380 mAh	
Battery Pack	Capacity	Approx. 300 splice and heat cycles	
,	Temperature	Recharge: 0 to 40 degree C	
	'	Storage : -20 to 30 degree C	
	Battery Life	Approx. 500 recharge cycles	
Display	LCD Monitor	TFT 5 inches with touch screen	
. ,	Magnification	200 to 320x	
Illumination	V-Grooves	LED lamp	
Interface	PC	USB2.0 Mini B type	
	External Led Lamp	USB2.0 A type, Approx. DC5V, 500 mA	
	Ribbon Stripper	Mini DIN 6 pin, DC12V, Max. 1A	
	Wireless	Bluetooth 4.1 LE	
	Splice Mode	100 splice modes	
Data Storage	Heat Mode	30 heat modes	
	Splice Result	20,000 splices	
C	Splice Image	100 images	
Screw Hole For Tripod		1/4-20 UNC	
Other Features	Automatic Functions	Splice mode select by fiber type analysis	
		Discharge power calibration	
		Wind protector : open/close	
		Sheath clamp : open	
		Heater lid : open/close	
		Heater clamp : open/close	
	2.6		
	Reference Guide	Video and PDF file stored in splicer	
	Reference Guide Sheath Clamp Electrode		